

Graphite crucible (For Common)

It is use to gold ,sliver ,copper ,beryllium and other non ferrous metal melting

Weight	Model	Φ1	Φ2	Φ3	H	In H	Ceramic shield are used in various purposes :	
1kg	SCC01	58	46	35	88	80	1) Melting Gold, Silver, Stainless Steel&PT	
2kg	SCC02	65	58	43	110	100	2) Labware	
2.5kg	SCC025	65	58	43	120	110	3) Testing equipment	
3kg	SCC03	85	75	60	105	95	4) Suggest Temperature: 2000-2200Degrees	
4kg	SCC04	85	75	60	130	118		
5kg	SCC05	100	88	70	130	118		
5.5kg	SCC055	104	90	70	155	140		
6kg	SCC06A	110	97	76	178	163	PARAMETER	
6kg	SCC06B	110	100	80	178	163	Bluk density	1.9g/cm3
8kg	SCC08	125	109	90	185	170	Purity :	99.98%
10kg	SCC10						Bending strength	55 Mpa
12kg	SCC12	150	134	100/ 105	210	190	Compressive	75Mpa
16kg	SCC16	160	138	110	220	200	Hardness:	40

SCJcermic.com 
Laboratory ceramic

